

## Nitinol

### Melt Practice

Nitinol is a family of alloys which are comprised of near equiatomic percentages of nickel and titanium. A few variants of Nitinol also include small amounts of a third element that is used to alter certain properties. Nitinol exhibits a thermoelastic martensitic transformation. This transformation is responsible for either shape memory or superelasticity being exhibited by the alloy. Following deformation below the transformation range, the ability called shape memory allows recovery of a predetermined shape upon heating above the transformation range. Superelasticity is the ability to recover a shape upon removal of an applied stress over a narrow range of deformation temperatures. The strain recovered with shape memory or superelasticity provides nearly ten times the elastic springback of other alloys such as stainless steel.

### Typical Chemistry

	FWM NiTi #1	FWM Avg.
Nickel	54.5-57.0 wt. %	56.0 wt %
Carbon	0.050 wt % Max.	0.033 wt % Max.
Oxygen	0.050 wt % Max.	0.028 wt % Max.
Hydrogen	0.005 wt % Max.	0.0025 wt % Max.
Titanium	Balance	Balance

*In addition to FWM's NiTi #1 (High Nickel Superelastic Binary), requirements for a variety of binary and ternary chemistries can be made available.*

### Physical Properties

*These values are typical for FWM NiTi#1*

	Austenite	Martensite
Density	6.45 g/cm <sup>3</sup>	6.45 g/cm <sup>3</sup>
Modulus of Elasticity	75GPa	40GPa
Electrical Resistivity	82x10 <sup>-6</sup> ohm-cm	76x10 <sup>-6</sup> ohm-cm
Magnetic Susceptibility	3.7x10 <sup>-6</sup> emu/g	2.4x10 <sup>-6</sup> emu/g
Coefficient of Thermal Expansion	11x10 <sup>-6</sup> /°C	6.6x10 <sup>-6</sup> /°C

### Transformation Properties

Because shape memory and superelasticity are very temperature dependent, there are a number of thermal points of interest that deserve discussion in order to gain an understanding of the material. This paper will discuss two of these points: the fully annealed austenitic peak and the active austenitic finish temperatures. The fully annealed austenitic peak (A<sub>p</sub>) is a temperature that FWM uses in order to classify the types of Nitinol. Several companies will make use of different points, but the intent of the measurements are the same. The A<sub>p</sub> is the point that the fully annealed Nitinol has the highest rate of transformation from Martensite to Austenite. The active austenitic finish temperature (Active A<sub>f</sub>) is a finished material property that is measured after heat treatment. This is the temperature at which the material has completely transformed to Austenite, which means that at and above this temperature the material will have completed its shape memory transformation or will display its superelastic characteristics. For a more detailed discussion of thermal properties and the effect that they may have on your finished product, please feel free to contact FWM.

<b>Fully Annealed Austenitic Peak (A p ) by Differential Scanning Calorimeter</b>	-25 to -5 °C
<b>Active Austenitic Finish (A f ) by bend and free recovery</b>	10 to 20 °C

## **Product Forms**

*Round Wire:* Size Range .0005" up to .250"

*Flat Wire:* Minimum thickness down to .0003"

*Strands and Cables:* Nitinol is available in all of our standard strand configurations.

*DFT (drawn filled tubing):* Please call FWM regarding your DFT needs.

*Turkshead and Specialty Shapes:* FWM has recently added the capability to manufacture your square, rectangle or other shaped cross-sectional wire needs.

## **Surface Finishes**

*Light Oxide:* (LO) Gold to Brown color - diamond drawn surface

*Dark Oxide:* (DK) Grey to Black color - diamond drawn surface

*Black Oxide:* (BLK) Shiny Black color - diamond drawn surface


*Etch:* (E) chemical removal of oxide layer - will retain smooth surface

*Pickled:* (P) chemical removal of oxide layer along with a slight amount of base metal - surface will have a rough texture

*Etched and Mechanically Polished:* (EMP) Chemical removal of oxide layer followed by mechanical polish - surface will have stainless steel appearance (although at >40x magnification, micro scratches will be present)

## **Mechanical Properties (at 21 +/- 3°C)**

Two critical characteristics unique to Nitinol in the austenitic phase are the loading plateau and the unloading plateau. The loading plateau stress is the stress level at which material at a specific temperature above A f will force Austenite phase into Martensite. This produces an almost constant stress level over a relatively large range of strain, up to about 8%. The unloading plateau stress is the stress level at which the Martensite will return to the Austenitic phase.



Typical Tensile Curve for Nitinol Wire at  $T > A_f$

Loading Plateau Stress (at 4% Strain)	75kpsi.
Unloading Plateau Stress (at 4% Strain)	35kpsi.
Permanent Set (after 6% Strain)	0.25%
Permanent Set (after 8% Strain)	0.50%
Ultimate Tensile Strength	>190kpsi
Elongation to Failure (as drawn)	5.0% approx.
Elongation to Failure (after 500°C Treatment)	>11%

### Typical Applications

Nitinol wire is used in a variety of medical device applications including guidewires, catheters, stents, filters, needles, guide pins, orthodontic appliances, endodontic files, stone retrieval baskets and stylets. Other commercial applications include eyeglass frames, cellular phone antennae and fishing tackle.